

Lengths of C-profile for Basic version - Bottom clamp attached optionally inwards or outwards

10				B15				15				R15			
10.5.038.0				B15.5.038.0				15.5.038.0				R15.025.100.0			
B_{Ri} [mm]	Part No. attached inwards	Part No. attached outwards		B_{Ri} [mm]	Part No. attached inwards	Part No. attached outwards		B_{Ri} [mm]	Part No. attached inwards	Part No. attached outwards		B_{Ri} [mm]	Part No. attached inwards	Part No. attached outwards	
.015	30	*	960.30.125	.015	30	*	960.30.125	.015	30	*	960.30.125	.025	40	*	960.30.150
.025	40	*	960.30.150	.025	40	*	960.30.150	.025	40	*	960.30.150	.038	80	*	960.30.150
.038	53	*	960.30.150	.038	53	*	960.30.150	.038	53	*	960.30.150	.063	80	*	960.30.175
.050	65	960.30.125	960.30.175	.050	65	960.30.125	960.30.175	.050	65	960.30.125	960.30.175	.080	98	960.30.150	960.30.200
.5	80	960.30.125	960.30.175	.5	80	960.30.125	960.30.175	.5	80	960.30.125	960.30.175				
.6	98	960.30.150	960.30.200	.6	98	960.30.150	960.30.200	.6	98	960.30.150	960.30.200				
.7	117	960.30.175	960.30.225	.7	117	960.30.175	960.30.225	.7	117	960.30.175	960.30.225				

*upon request