

Superior Clamping and Gripping



## **Product Information**

Gripper for small components EGP 64

# High Performance Density. Fast. Compact. Gripper for small components EGP

Electric 2-finger parallel gripper with smooth-running base jaws guided on roller bearings

## Field of application

Gripping and moving of small to medium-sized workpieces with flexible force and high speed in clean environments, such as assembly, testing, laboratory and pharmaceutical industry

## **Advantages – Your benefits**

**Highest performance density** for the use of smaller grippers sizes

**Control via digital I/O** for easy commissioning and rapid integration into existing systems.

**Two to four stage adjustable gripping force** for simple adaption to sensitive workpieces

**Backlash-free, pre-loaded cross roller guide** for precise gripping with nearly constant force for all permissible finger lengths

**Very high maximum cycles per minute** for highest productivity

**Compact dimensions** for minimal interfering contours in the application

**Proven a thousand times MPG-plus basis** for equal gripping forces and strokes with identically high efficiency

**Brushless DC servomotor** for almost wear-free use and a long service life

**Control via IO-Link** Enables pre-positioning of the gripper finger and evaluation of the gripper condition as well as the adjustability of special gripping modes.

**NEW: food-grade lubrication** as a solution for an easy entry into medical technology, lab automation, pharmaceutical and food industry













## **Functional description**

The brushless servomotor drives the base jaw via the gear mechanism.

The jaw stroke is synchronized by means of rack and pinion kinematics.



- Base Jaw for the connection of workpiece-specific gripper fingers
- ② Cross roller guidance precise gripping due to backlash-free base jaw guidance
- ③ Gear Rack and pinion principle for centric gripping
- **Drive**Brushless DC servomotor
- © Control electronics Integrated control and power electronics for decentralized control of the servomotor

#### General notes about the series

**Operating principle:** Rack and pinion principle **Housing material:** Aluminum alloy, coated

Base jaw material: Steel

Actuation: servo-electric, via brushless DC servomotor

Warranty: 24 months

**Scope of delivery:** Accessory kit for centering sleeves, bracket for proximity switch, assembly instructions.

**Gripping force:** is the arithmetic sum of the individual force applied to each jaw at distance P (see illustration).

**Finger length:** is measured from the reference surface as the distance P in direction to the main axis.


**Repeat accuracy (gripping):** defined as the spread of the actual position at 100 consecutive closing or opening movements on a rigid workpiece or a fixed workpiece stop under constant conditions.

**Repeat accuracy (positioning, unidirectional):** defined as the spread of the actual position of the base jaws after 100 consecutive movements to a target position from the same direction under constant conditions.

**Repeat accuracy (positioning, bi-directional):** defined as the spread of the actual position of the base jaws after 100 consecutive movements to a target position from both directions under constant conditions.

**Workpiece weight:** is calculated for force-fit gripping with a coefficient of static friction of 0.1 and a safety factor of 2 against workpiece slippage at acceleration due to gravity g. For form-fit or capture gripping, there are significantly higher permissible workpiece weights.

**Closing and opening times:** are purely the times that the base jaws or fingers are in motion. PLC reaction times are not included in the above–mentioned times and must be taken into consideration when determining cycle times.



## **Application example**

Pick & place unit driven by linear motor for dynamic movements.

- Pillar assembly system
- Electric linear module ELP
- Selectric 2-finger parallel gripper EGP

### SCHUNK offers more ...

The following components make the product even more productive – the suitable addition for the highest functionality, flexibility, reliability, and controlled production.



① For more information on these products can be found on the following product pages or at schunk.com.

## Options and special information

**Manually adjustable gripping force:** With an integrated rotary switch, the gripping force can be adjusted in two stages for the EGP 25 to 100% and 50%, and in four stages for EGP 40, 50 and 64 to 100%, 75%, 50%, and 25%.

**Version with IO-Link:** The integration of IO-Link makes it possible to adjust the gripping force, to pre-position the gripper fingers and to evaluate the gripper status.

**New! Gripping modes with IO-Link:** In addition to a cycle time-optimized gripping mode (FastGrip), the IO-Link version also offers a gripping mode with pulse reduction of the gripping force (SoftGrip) for gripping fragile workpieces.

**Speed version S:** for faster closing and opening times due to the use of a different gear ratio. The option of a gripping force adjustment is no longer available.

Optional status monitoring via external sensor system: The status of the gripper can be monitored by external sensors.


Optional adapter plates: Space saving, front-end fastening of the gripper is enabled by optional adapter plates.

**KA connection cable:** Connection cables with an angled or a straight female connector can be ordered in various lengths to connect the gripper with the power supply and higher–level control system.


Food-grade lubrication: The requirements of EN 1672-2:2020 are not fully met.




#### **Gripping force**



#### **Gripping modes with IO-Link**



#### **Dimensions and maximum loads**




The indicated moments and forces are statical values, apply for each base jaw and may appear simultaneously. Loads may additionally occur to the moment produced by the gripping force itself.

#### Technical data

Description		EGP 64-N-N-B
ID		0310980
General operating data		
Stroke per jaw	[mm]	10
Min./max. gripping force	[N]	75/300
Recommended workpiece weight	[kg]	1.25
Max. permissible finger length	[mm]	80
Max. permissible mass per finger	[kg]	0.24
Repeat accuracy (gripping)	[mm]	0.02
Closing/opening time	[s]	0.49/0.49
Weight	[kg]	0.8
Min./max. ambient temperature	[°C]	5/55
IP protection class		30
Cleanroom class ISO 14644-1:1999		5
Noise emission	[dB(A)]	<70
Dimensions X x Y x Z	[mm]	64 x 35 x 114.7
Electrical operating data		
Nominal voltage	[V]	24
Nominal current	[A]	0.15
Max. current	[A]	2
Controller electronics		integrated
Communication interface		Digital inputs
Number of digital I/O		21-
Options and their characteristics		
Version with IO-Link		1383545
Weight	[kg]	0.83
Specification		V1.1
Transmission rate		COM2
Port		Class B
Repeat accuracy (positioning, unidirectional)	[mm]	±0.2
Repeat accuracy (positioning, bi-directional)	[mm]	±0.2
Gripping modes		FastGrip, SoftGrip


#### Main view




The drawing shows the basic version of the gripper with open jaws, without dimensional consideration of the options described below.

- 1 Gripper connection
- 2 Finger connection
- **50** Electrical connection
- 80 Depth of the centering sleeve hole in the counter part


#### Maximum permitted finger projection





Lmax is equivalent to the maximum permitted finger length, see the technical data table.


#### Jaw design



- 90 Vertically positioned prism
- (91) Horizontally positioned prism

A workpiece, which is gripped using three points of contact, can be reliably gripped with high repeatability. A system with more than three points of contact is overdetermined. The drawing shows two alternative gripper finger designs for coaxial and radial gripping of a cylindrical part.


#### 10-Link version IOL



90 M12, 5-pin

The position of the gripper fingers and the gripping force can be set flexibly on the IO-link version. The drawing shows dimensional changes of the IO-Link version compared to the basic version found in the main view.

#### **Adapter plate**




- 1 Gripper connection72) Fit for centering sleeves
- 80 Depth of the centering sleeve hole in the counter part
- The adapter plate includes an O-ring\* for a direct air connection, additional centering sleeves, and screws for mounting the gripper. \*Optional only with pneumatic actuators

Description	ID	
Adapter plate		
APL-MPG-plus 64	0305547	

 $\ensuremath{\textcircled{\scriptsize 1}}$  The adapter plate is a separately ordered, optional accessory.

#### Adapter plate




(81) Not included in the scope of delivery

The adapter plate includes an 0-ring\* for a direct air connection, additional centering sleeves, and screws for mounting the gripper. \*Optional only with pneumatic actuators

Description	ID
Adapter plate	
APL-MPG-plus 64	0305547

① The adapter plate is a separately ordered, optional accessory.

#### Finger blanks with BSWS ABR-BSWS-MPG-plus 64




2 Finger connection

90 Machining volume

Finger blanks for customized subsequent machining with integrated jaw quick-change system for precise and fast finger changes.

Description	ID	Scope of delivery					
Finger blank with jaw quick-change system							
ABR-BSWS-MPG-plus 64	0302898	2					




(73) Fit for centering pins

The drawing shows the finger blank which can be reworked by the customer.

Description ID		Material	Scope of delivery		
Finger blank					
ABR-MPG-plus 64	0340215	Aluminum (3.4365)	2		

#### Finger blanks with BSWS




90 Included in the scope of delivery

The finger blanks with jaw quick-change system allow fast and manual gripper finger changes. The mechanical interface to the gripper is already integrated. Only the specific workpiece geometry needs to be machined into the finger blank.

Description	ID	ope of delivery						
Finger blank with jaw quick-change system								
ABR-BSWS-MPG-plus 64	0302898	2						


#### **Modular Assembly Automation**



- (4) Grippers
- 90 ASG adapter plate
- (91) CLM/KLM/LM/ELP/ELM/ELS/HLM linear modules

Grippers and linear modules can be combined with standard adapter plates from the modular assembly system. For more information see our main catalog "Modular Assembly Automation".

#### IN 40 inductive proximity switches



(17) Cable outlet


90 Inductive proximity switches

Directly mounted end position monitoring.

Description	ID	Often combined
Inductive proximity switches		
IN 40-S-M12	0301574	
IN 40-S-M8	0301474	•
INK 40-S	0301555	
Connection cables		
KA BG08-L 3P-0300-PNP	0301622	•
KA BG08-L 3P-0500-PNP	0301623	
KA BG12-L 3P-0500-PNP	30016369	
KA BW08-L 3P-0300-PNP	0301594	
KA BW08-L 3P-0500-PNP	0301502	
KA BW12-L 3P-0300-PNP	0301503	
KA BW12-L 3P-0500-PNP	0301507	
clip for plug/socket		
CLI-M12	0301464	
CLI-M8	0301463	
Cable extension		
KV BG12-SG12 3P-0030-PNP	0301999	
KV BG12-SG12 3P-0060-PNP	0301998	
KV BW08-SG08 3P-0030-PNP	0301495	
KV BW08-SG08 3P-0100-PNP	0301496	
KV BW08-SG08 3P-0200-PNP	0301497	•
KV BW12-SG12 3P-0030-PNP	0301595	
KV BW12-SG12 3P-0100-PNP	0301596	
KV BW12-SG12 3P-0200-PNP	0301597	
Sensor distributor		
V2-M12	0301776	•
V2-M8	0301775	•
V4-M8	0301746	
V8-M8	0301751	

Two sensors are required per unit for monitoring two positions. On option, extension cables and sensor distributors are available. Additional product variants of the sensor, and further information and technical data can be found in the catalog chapter sensor system.

#### **Attachment kit for FPS**




The following FPS position sensor can differentiate between five programmable areas or switching points for the stroke of a gripper, and can be used in connection with a PC as a measuring system.

Description	ID
Attachment kit for	FPS
AS-FPS-MPG 64	0301764

① This attachment kit needs to be ordered optionally as an accessory.

#### Flexible position sensor



90 FPS-S sensor


(91) FPS-F5 evaluation electronic

Flexible position monitoring of up to five positions.

Description	ID	Often combined
Attachment kit for FPS		
AS-FPS-MPG 64	0301764	
Sensor		
FPS-S 13	0301705	
Evaluation electronics		
FPS-F5	0301805	•
Cable extension		
KV BG08-SG08 3P-0050	0301598	
KV BG08-SG08 3P-0100	0301599	

When using an FPS system, an FPS sensor (FPS-S) as well as an electronic processor (FPS-F5 / F5 T) are required for each gripper as well as a mounting kit (AS), if listed. Cable extensions (KV) are optionally available – see catalog chapter "Accessories."

#### 10-Link connection cable



KA G... KA W... Connection cable with straight socket Connection cable with angular socket


- 6 Connection module side
- 15 Socket
- 90 SAC connection cable with open wire strands
- 91) Connection plug component
- (92) Cable with straight female connector
- (93) Cable with angled female connector

The connection cable is ideal for connecting the corresponding components to the control system. The connection cable has a 5-pin M12 socket on one side, and open wire strands on the other side for individual connections. The connection cables are suitable for use both in the cable track as well as in torsion applications.

Description	ID	L1	D1	L2	D2	L3	D3
		[m]	[mm]	[mm]	[mm]	[mm]	
10-Link connection cable - dra	IO-Link connection cable – drag chain and torsion-compatible						
KA GLN1205-IOL-00500-A	1387207	5	4.8	38	15		M12
KA GLN1205-IOL-01000-A	1387209	10	4.8	38	15		M12
KA WLN1205-IOL-00500-A	1387210	5	4.8	39	15	28	M12
KA WLN1205-IOL-01000-A	1387211	10	4.8	39	15	28	M12

① Please observe the min. bending radius for cable track-compatible cables or the max. torsion angle for torsion-compatible cables. These are generally 10 times the cable diameter or +/- 180°/m.

#### **Connection cables**



KA G... KA W... Connection cable with straight socket Connection cable with angular socket


- 6 Connection module side
- (15) Socket
- 90 SAC connection cable with open wire strands
- (91) Connection plug component
- (92) Cable with straight female connector
- (93) Cable with angled female connector

The connection cable is ideal for connecting the corresponding components to the controller or the power supply unit. The connection cable has a 4-pin M8 socket on one side and an open wire strand on the other side for individual connections. The connection cables are suitable for use both in the cable track as well as in torsion applications.

Description	ID	l1	D1	L2	D2	L3	D3	Often combined
		[m]	[mm]	[mm]	[mm]	[mm]		
Connection cable – suitable	for drag chain:	s and a high torsion	resistance					
KA GLN0804-10-00200-A	1310371	2	4.8	33.7	10		M8	
KA GLN0804-10-00500-A	1310375	5	4.8	33.7	10		M8	•
KA GLN0804-I0-01000-A	1310379	10	4.8	33.7	10		M8	
KA WLN0804-10-00200-A	1310372	2	4.8	27.9	10	18.9	M8	
KA WLN0804-10-00500-A	1310376	5	4.8	27.9	10	18.9	M8	
KA WLN0804-I0-01000-A	1310381	10	4.8	27.9	10	18.9	M8	

Please observe the min. bending radius for cable track-compatible cables or the max. torsion angle for torsion-compatible cables. These are generally 10 times the cable diameter or +/- 180°/m.

#### 10-Link cable extension



KV G... KV W... Cable extension with straight socket

Cable extension with angled socket

- 6 Connection module side
- 15 Socket
- 90 Cable end with straight connector
- (91) Connection plug component
- (92) Cable with straight female connector
- (93) Cable with angled female connector

The cable extensions are ideal for connecting the relevant components to the control system, or for use as extension cables. The cable extensions have a 5-pin M12 connector with a straight or angled design on the module side and a 5-pin M12 plug with a straight design on the other side. The cable extensions are suitable for use in the cable track and in torsion applications.

Description	ID	L1	D1	L2	D2	L3	D3
		[m]	[mm]	[mm]	[mm]	[mm]	
10-Link cable extension – cabl	10-Link cable extension – cable track and torsion-compatible						
KV GGN1205-IOL-00200-A	1387195	2	4.8	41	15		M12
KV GGN1205-IOL-00500-A	1387199	5	4.8	41	15		M12
KV WGN1205-IOL-00200-A	1387202	2	4.8	39	15	28	M12
KV WGN1205-IOL-00500-A	1387205	5	4.8	39	15	28	M12

① Please observe the min. bending radius for cable track-compatible cables or the max. torsion angle for torsion-compatible cables. These are generally 10 times the cable diameter or +/- 180°/m.



SCHUNK GmbH & Co. KG Spann- und Greiftechnik

Bahnhofstr. 106 - 134 D-74348 Lauffen/Neckar Tel. +49-7133-103-0 Fax +49-7133-103-2399 info@de.schunk.com schunk.com

Folgen Sie uns | Follow us









